

## Product Description

The Zonda Over the Bed light is fixed by a bracket to the rear of the bed head board and curls over the top of it. The light which features a flexible stem to allow it to be positioned as required.

## Metal finish

The light comes in the following metal finishes:

- Clear Anodised Aluminium
- Anodised Titanium
- Anodised Bronze
- Polished Nickel Plate
- Gold Plate

## Leather finish

The light comes in the following leather finishes:

- Chocolate
- Beige
- Black
- Mushroom
- Off White

## Dimensions

Depth/605mm  
Bracket Depth/32mm

## Electrical



The light uses 1.2 Watts of energy and requires a 12v DC power Supply.

The Zonda light is available in the following switching mode and LED colours.


- Warm White/High, Medium, Off
- Cool White/High, Medium, Off

## Additional information

The Zonda Over the Bed Mount light requires a driver for installing on a Mains voltage circuit. This driver should be installed remotely in a suitable area behind the fitting.



MOUNTING BRACKET  
Dimensions in mm



MOUNTING HOLES  
Dimensions in mm