# Beadlight

Zephyr Range/Technical Data Sheet


### **ZEPHYR**

SLIM (INTEGRAL BEZEL)









## **Product Description**

The Zephyr Slim Integral Bezel light is fixed by a mounting ring at the rear of the bed head board. The light is neatly presented through a recess in the bedhead. The lamp can be rotated left and right allowing control of the beam position.

#### Metal finish

The light comes in the following metal finishes:

- Clear Anodised Aluminium
- Anodised Titanium
- Anodised Bronze
- Polished Nickel Plate
- Gold

#### Dimensions

Depth/39.5mm Light Diameter/80mm Tail Length/500mm

#### Electrical

The light uses 1.7 Watts of energy and requires a 12v DC power Supply.

The Zephyr light is available in the following LED colours.

- Warm White
- Cool White

#### Additional information

The Zephyr Slim Integral Bezel light requires a driver for installing on a Mains voltage circuit. This driver should be installed remotely in a suitable area behind the fitting.

01993 868866

Web: www.beadlight.com Email: contact@beadlight.com

### M4 Pan Hd. RECOMMENDED APERTURE FOR INSTALLATION Dimensions in mm LIGHT OFF LIGHT ON LIGHT OFF FRONT LIGHT ON FRONT REAR VIEW